

# **PS 360.X7 Precision Balance**





The drawings, photos and graphics used are for illustrative purposes only.

## **Functions**

Ø	Autotest		Dosing	%	Percent Weighing	•••	Parts counting
MAX	Peak hold		Formulation	<b>/</b>	Newton unit measurement	<u>.al</u>	Statistics
- <b>0</b> K+	Checkweighing	4	IR sensors	\$	Under-pan weighing	GLP	GLP Procedures
4	Animal weighing	ρ	Density determination		Ambient conditions monitoring	G	Replaceable unit
SQC	Statistical Quality Control		ALIBI Memory	Ш	Mass for titrator		Wi-Fi

## **Datasheet**

Metrological parameters					
Maximum capacity [Max]	360 g				
Minimum load	20 mg				
Readability [d]	1 mg				
Verification unit [e]	10 mg				


Metrological parameters	
Tare range	-360 g
Standard repeatability [5% Max]	0.5 mg
Standard repeatability [Max]	1 mg
Standard minimum weight (USP)	1 g
Standard minimum weight (U=1%, k=2)	0.1 g
Linearity	±2 mg
Stabilization time	2 s
Adjustment	internal (automatic)
OIML Class	II
Sensitivity temperature drift	2×10 <sup>-6</sup> /°C×Rt
Physical parameters	
Leveling system	manual
Display	7" graphic colour touchscreen
Delivery components	Balance, weighing pan, weighing pan shield, grounding bumper ×1, bumper ×3, power supply.
Weighing pan dimensions	128×128 mm
Packaging dimensions	545×455×575 mm
Net weight	3.99 kg
Gross weight	5 kg
Construction	
Protection class	IP 43
Components and software	
Database capacity	7
Features of use	
Touch-free operation	2 IR Sensors
Communication interface	
Communication interface	2×RS232 <sup>1</sup> , USB-A, USB-B, Ethernet, Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Balance: 12 – 15V DC 0.8A max
Power consumption	4 W
Environmental conditions	
Operating temperature	+10 ÷ +40 °C
Ambient conditions monitoring (option)	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Relative humidity	40% ÷ 80%

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

<sup>&</sup>lt;sup>1</sup> Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

<sup>\*</sup> Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



#### **Accessories**

Balance Storage Case
Antivibration Tables
Power Adapters
Cigarette lighter receptacle power supply cables
USB cable (scale - printer)
Density determination KIT
Barcode scanners
Anti-Draft Chamber for Balances with a 128×128 mm Weighing Pan
RS 232, RS 485 cables
THBR 2.0 System - Ambient Conditions Monitoring

Displays
Receipt Printer
Protective cover for balances
RS 232, RS 485 cables
Additional modules
Protective cover for balances
Under-pan weighing
RS 232 cables (scale - printer)
RS 232 - RS 485 Converter

### **Software**

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]
- · Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

### **Device dimensions**

